



Liquid Laundry 48

DESCRIPTION

This is a concentrated non-built liquid laundry detergent, which is designed to be equally effective in hot or cold water. This detergent is formulated only for multi-component automatic dispensing systems where the toughest, most troublesome laundry problems exist and is not recommended for fine or delicate fabrics. This product contains, **optical brighteners**, fast acting cleaning agents, water based solvents and is effective on natural and synthetic fibers. Highly concentrated for use in hotels, motels, schools, hospitals, and nursing homes. It also provides a thorough cleaning by preventing redeposition of particulate, which can cause discoloration and break down in the strength of fabrics. Cleaning is provided through the use of modified detergents rather than strong alkaline booster compounds.

INSTRUCTIONS

Always follow garment manufacturers general washing instructions to retain quality of garment. This modern controlled suds formula is designed to act quickly to break down stubborn dirt grease and oils. For general laundry usage (top load machines) use approximately 3 ounces per load for larger loading machines or for heavier soiled loads use 4 ounces per load. Automatic dispensing units are most widely used today for simplicity, due to the fact that they are programmed to deliver exactly the amount needed for different sized loads and solid levels. In most cases, the average 50-pound commercial machine will require 4 to 8 ounces per load.

FEATURES

- Fortified with Optical Brightener
- Economical highly concentrated
- Formulated for multi-component systems
- Contains anti-redeposition ingredients
- Cleans with built modified detergents
- Controlled suds
- Quickly breaks down greases and oils
- Rinses freely and completely

SPECIFICATIONS

Appearance: BLUE
Odor: PLEASANT
Specific gravity: 1.02-1.06
pH: 9.0-10.0
Detergency: Excellent

SAFETY

Keep out of reach of children. Product contains alkalis. Although this product will clean most clothing very well, many materials are possibly degraded by alkaline detergents, and may show surface dulling. Also use with caution on white metals such as aluminum. Read material data safety sheet for further safety precautions.